

Pluggable Terminal Blocks

3.5 mm Pitch



FEATURES:

Polarised mouldings
Closed headers
Guided pin alignment
Pin/terminal - Tinned phosphor bronze
Rising clamp - Nickel copper flash brass
Screw/torque - M2 steel Tin plated, 0.3Nm
Recommended PCB hole size ϕ 1.2 mm
cUL approved

SPECIFICATION:

Gender of contacts	Female
Rated current to EN	10 A
Pitch	3.5 mm
Termination type	Screw Connection
Connection direction	vertical
Rated voltage to EN	200 V
Combustibility class	UL 94 V-0
Colour	green
Temperature range	-33...+120 °C
Cross-section max.	1.3 mm ²
Cross-section min.	0.13 mm ²
Connection cross-section	0.13-1.3 mm ² (26-16AWG)



PRODUCT RANGE:

Art. Nr.	Poles	Length
RND 205-00089	2	7 mm
RND 205-00090	3	10.5 mm
RND 205-00091	4	14 mm
RND 205-00092	5	17.5 mm
RND 205-00093	6	21 mm
RND 205-00095	8	28 mm
RND 205-00096	9	31.5 mm

