

Crimp Fittings

Press-armaturen


Embouts sertis

Raccordi a graffare

Racores para presión

FJ

J.I.C Female Swivel
 JIC-Dichtkopf
 Femelle JIC
 Femmina girevole JIC
 Hembra loca JIC



Part Number	Part Number	Part Number	Thread T	Flange	Tube O.D.	ND	Hose Size	A	D	H	E Ø	HEX [1]	HEX [2]	K Ø
OTC Fitting	Skive Nipple	TTC Fitting			mm			mm	mm	mm	mm			mm
1G3FJ3	1S3FJ3	1A3FJ3	3/8-24				-3	34,3	16,9		2,5	14	11	
1G4FJ3	1S4FJ3	1A4FJ3	7/16-20				-3	33,6	16,1		2,5	14	11	
1G4FJ4	1S4FJ4	1A4FJ4	7/16-20				-4	41,4	18,0		4,2	14	14	
1G5FJ4	1S5FJ4	1A5FJ4	1/2-20				-4	41,8	18,4		4,2	17	14	
1G4FJ5	1S4FJ5	1A4FJ5	7/16-20				-5	42,2	18,3		5,3	14	14	
1G5FJ5	1S5FJ5	1A5FJ5	1/2-20				-5	42,7	18,8		5,3	17	14	
1G6FJ5	1S6FJ5	1A6FJ5	9/16-18				-5	45,5	21,6		5,3	17	17	
1G5FJ6	1S5FJ6	1A5FJ6	1/2-20				-6	46,7	21,4		6,7	17	17	
1G6FJ6	1S6FJ6	1A6FJ6	9/16-18				-6	47,8	22,5		6,7	17	17	
1G8FJ6	1S8FJ6	1A8FJ6	3/4-16				-6	49,1	23,8		6,7	22	17	
1G8FJ8	1S8FJ8	1A8FJ8	3/4-16				-8	55,4	25,7		9,6	22	22	
1G10FJ8	1S10FJ8	1A10FJ8	7/8-14				-8	69,7	40,0		9,6	27	22	
1G10FJ10	1S10FJ10	1A10FJ10	7/8-14				-10	57,0	27,6		12,8	27	24	
1G12FJ10	1S12FJ10	1A12FJ10	1 1/16-12				-10	54,8	25,4		12,8	32	27	
1G10FJ12	1S10FJ12	1A10FJ12	7/8-14				-12	58,2	28,0		15,5	27	30	
1G12FJ12	1S12FJ12	1A12FJ12	1 1/16-12				-12	57,7	27,5		15,5	32	30	
1G16FJ12	1S16FJ12	1A16FJ12	1 5/16-12				-12	63,6	33,3		15,5	41	32	
1G12FJ16	1S12FJ16	1A12FJ16	1 1/16-12				-16	65,6	31,2		20,7	32	36	
1G16FJ16	1S16FJ16	1A16FJ16	1 5/16-12				-16	68,3	33,9		20,7	41	36	
1G20FJ16	1S20FJ16	1A20FJ16	1 5/8-12				-16	64,3	29,9		20,7	50		
1G20FJ20	1S20FJ20	1AP20FJ20*	1 5/8-12				-20	75,6	31,6		26,6	50		
		1AT20FJ20**	1 5/8-12				-20	75,6	31,6		26,6	50		
1G24FJ24	1S24FJ24	1A24FJ24	1 7/8-12				-24	80,3	33,9		32,0	60		
		1A24FJ32					-32	85,3	33,1		44,4	60		
1G32FJ32	1S32FJ32	1A32FJ32	2 1/2-12				-32	86,8	34,6		44,4	75		

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire

* 1-wire
 ** 2-wire