

MB CAP ULTRA BUFFER MODULE

IN: 24VDC OUT: 24VDC/20A for max. 1A/320S


INPUT: 24 V DC (SELV/PELV)


OUTPUT: max. 20 A

Buffer time: 16 s

[Link to Product](#)

Illustration





Product may differ from Image

Approvals



Input

Input voltage	24...26.4 V DC
Input current	20 A
Inrush current	max. 36.5 A
Loading time	typ. 40 s; max. 500 s

General data

Standards	(EN 60950-1), (EN 61204-3), (EN 55011 A)
Mounting method	DIN-rail mountable TH35-7.5/TH35-15 (EN 60715)
Efficiency	90 %
Temperature range	-20...+60 °C (storage temperature -20...+60 °C)

Output

Output voltage	23.3 V DC ± 2 %
Output current	max. 20 A (+60 °C)
Buffer time	16 s (20 A); 320 s (1 A)

Commercial data

country of origin	DE
customs tariff number	85322900
minimum order quantity	1