





















Plugs



*System Article type	Technical Data	Order no. Colour	*System Article type	Technical Data	Order no. Colour
 <p>SLS 200</p>	 <p>30 A 300 V screw connection up to 2.5 mm²</p>	<p>932 153-100 ●</p> <p>932 153-101 ●</p>	 <p>KUN S</p>		<p>934 096-100 ●</p> <p>934 096-101 ●</p> <p>934 096-102 ●</p> <p>934 096-103 ●</p> <p>934 096-104 ●</p>
 <p>MST 3</p>	 <p>6 A solder contact</p>	<p>973 509-100 ●</p> <p>973 509-101 ●</p> <p>973 509-102 ●</p> <p>973 509-103 ●</p> <p>973 509-104 ●</p> <p>973 509-106 ●</p>	 <p>KUN 30</p>	 <p>16 A solder contact up to 2.5 mm²</p>	<p>931 804-100 ●</p> <p>931 804-101 ●</p> <p>931 804-102 ●</p> <p>931 804-103 ●</p> <p>931 804-104 ●</p>
 <p>VST 20</p>	 <p>16 A solder contact max. 2 mm²</p>	<p>930 050-000</p>	 <p>KUN 10</p>	 <p>16 A screw connection up to 1.5 mm²</p>	<p>930 189-100 ●</p> <p>930 189-101 ●</p>
 <p>VST 100</p>	 <p>16 A screw connection max. 1.5 mm²</p>	<p>930 581-000</p>	 <p>MKU 1</p>	 <p>6 A</p>	<p>930 320-100 ●</p> <p>930 320-101 ●</p>
 <p>MST 201</p>		<p>931 338-001</p>	 <p>KD 10</p>	 <p>10 A</p>	<p>930 109-100 ●</p> <p>930 109-101 ●</p>

* System: (64) = 0.64 mm system / (2) ≙ 2 mm system / (4) ≙ 4 mm system / (●) ≙ 4 mm safety system / (↔) ≙ 4 mm sliding sleeve system