

Product data sheet

Item No. 92.207.3000.3

Cable assembly GST1814KSBS 15 30GR01

geis® Extension cable female - male; length: 3m; type GST1814; 4-pole; 250/400 V / 16 A; colour of coding: grey with black strain-relief; cable: H05VV-F 4G1,5, colour: black



Item No.	92.207.3000.3
EAN	4015573569522
Order Unit	20 Piece(s)

Certificates / Approvals



Technical data

General

Rated current	16 A
Rated voltage	400 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Code 2
Interlockable	Yes
Color of coding/ contact carrier	Pebble gray
Marking of poles	
Color of housing inclusive strain relief	Black

Model

Number of poles	4
Nominal cross section conductor	1.5 mm <sup>2</sup>
Degree of protection (IP)	IP40
Cable type	H05VV-F
Cable colour	Black
Cable diameter	9.2 mm
Version of cable	Female - male



Type of cord set	Connecting cable
Version cable end 1	GST18i4 socket
Version cable end 2	GST18i4 plug

**Material**

Surface finish	Tin-plated
Halogen free	No
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

**Dimensions**

Total length	3 m
--------------	-----

**Technical drawing**

Pol	Aderfarbe
pole	colour of core
L1	braun / brown
⊖	grün-gelb / green-yellow
N	blau / blue
L2	schwarz / black

  

.F	Farbe colour	Codierung *X* Buchse female	Codierung *Y* Stecker male	Kabelfarbe / cable colour Zugentlastungsfarbe/strain relief colour
.1	schwarz black	2 N PE 1	1 PE N 2	schwarz black
.2	weiß white	2 N PE 1	1 PE N 2	weiß white
.3	grau grey	2 N PE 1	1 PE N 2	schwarz black

  

Teile-Nr. part-no.	L	Beispiel (Farbe: schwarz) example (colour: black)	Typ type
92.207.XX00.F	XX in dm-Schritten	92.207.1000.1 = 10dm/L= 1000mm	GST18i4KSBS 15 10SW
U2.207.XX00.F	XX in m-Schritten	U2.207.1200.1 = 12 m/L=12000mm	GST18i4KSBS 15 X10SW

Weitere Daten siehe Katalog  
further data see catalog

Typ/type: GST18i4KSBS 15 .. SW = schwarz/black  
WS = weiß/white  
GR01 = grau/grey