

Threaded connector

For COOL-LINE® jointed hose systems

ARIANA

Application:


For adapting jointed hose systems to various female threads.

Version:

- Made from high-quality and robust plastic
- Max. 6 bar operating pressure
- 1/4" version approx. 15 l/min. Flow rate
- 1/2" version approx. 28 l/min. Flow rate

Advantage:

- Chemical-resistant, does not conduct electricity
- Compatible with almost all conventional systems without an adapter



Art. no.	18300 820
System design	1/2 inch
Type	Threaded connector R 1/2"
Outlet diameter	12.7 mm
Included in delivery	4 units