

Table trolley with push handle, load capacity 300 kg

With two and three wooden load areas

Application:

For transporting goods and materials, for normal requirements in terms of load-bearing capacity and resistance.

Version:

- Welded steel tube and profile steel, bolted construction
- Shelves made of wooden plate, beech decoration surface, mounted in steel frames
- Shelves with 12 mm high edge
- High sliding handle
- Carrying capacity of upper loading area 80 kg

Advantage:

- Very versatile
- Ergonomic push handle height



Art. no.	50258 543
Material of loading surface	Wood
Load-carrying capacity	300 kg
Length	1136 mm
Length x width x height	1136 x 611 x 1039 mm
Load-carrying capacity of loading surfaces	80 kg
Number of loading surfaces	3
Loading surface size	1000 x 600 mm
Loading surface length	1000 mm
Loading-surface width	600 mm
Loading-surface height	200 mm, 510 mm, 820 mm
Height	1039 mm
Number of fixed rollers	2
Number of steering rollers	2
With wheel lock	Yes
Total stop optional	Yes
Wheel width	32 mm
Wheel diameter	125 mm
Material of wheel	TPE
Colour	Anthracite grey RAL 7016
Surface	Powder-coated
Colour of loading area	Medium grey

EAN-Code

4017976327525