

## Electronically temperature-controlled soldering station ANALOG 60

150–450° adjustable



### Application:

For professional soldering tasks.

### Execution:

- Voltage 230 V, 50/60 Hz
- Noise-suppressed
- 24-V secondary voltage
- Temperature measured with thermosensor
- Potential equalisation socket (connected to the soldering tip with high resistance)
- Multi-functional support rest
- With 2-m connection cable



<b>Art. no.</b>	<b>54372 010</b>
<b>Brand</b>	ERSA
<b>Manufacturer Part Number</b>	0ANA60
<b>Type</b>	ANALOG 60
<b>Type description</b>	0832 CDLF
<b>Power rating</b>	60 W
<b>Min./max. temperature conditions</b>	150 to 450 °C
<b>Heat-up time</b>	60 s
<b>Tip diameter</b>	2.2 mm
<b>Shape of tip</b>	Chisel-shaped
<b>Gross Weight</b>	2.500 kg
<b>Product Group</b>	5JN

### EAN

4003008054866