

Electronically temperature-controlled soldering station ANALOG 60

150–450° adjustable



Application:

For professional soldering tasks.

Version:

- Voltage 230 V, 50/60 Hz
- Noise-suppressed
- 24-V secondary voltage
- Temperature measured with thermosensor
- Potential equalisation socket (connected to the soldering tip with high resistance)
- Multi-functional support rest
- With 2-m connection cable



Art. no.	54372 010
Type	ANALOG 60
Type description	0832 CDLF
Power rating	60 W
Min./max. temperature conditions	150 to 450 °C
Heat-up time	60 s
Tip diameter	2.2 mm
Shape of tip	Chisel-shaped

EAN-Code

4003008054866