

Kunststoffschuttschlauch kunststoffummantelter Federstahldrahtwendel

Farbe Grau
Sonderfarben auf Anfrage

Aufbau
Wendelgewellter Kunststoffschlauch
kunststoffummantelter Federstahl-
drahtwendel, Weich-PVC-Mantel

Material
Außenmantel PVC
Innenwendel PVC-ummantelter
Federstahldraht

- Eigenschaften**
- Hochflexibel
 - dehn- und stauchbar
 - luft- und flüssigkeitsdicht
 - weitgehend säure- u. ölbeständig
 - silikon- und cadmiumfrei
 - innerer Korrosionsschutz
 - geprüft nach DIN EN ICE 61386-23

Protective plastic conduit helix of PVC-sheathed spring steel wire

Colour grey
Special colours on request

Structure
Helical coiled corrugated plastic
conduit, helix of PVC sheathed
spring steel wire, soft PVC sheathing

Material
Sheathing PVC
Inside helix PVC sheathed spring
steel wire

- Properties**
- Extremely flexible
 - expansible and upsettable
 - air and liquidproof
 - widely resistant to oil and acids
 - free of silicone and cadmium
 - inside protection against corrosion
 - approved acc. to
DIN EN ICE 61386-23



Anwendungsgebiete

- Maschinen- und Anlagenbau
- Fahrzeugbau
- Schiffsbau
- Automation
- Elektroanlagen
- Einsatz in Führungsketten
- Als Saugschlauch geeignet

Application

- Machine and Plant Constructions
- Automotive
- Shipbuilding
- Automation
- Electrical Installations
- Applications with guide chains
- Suitable as suction conduit



Passende Verschraubungen Suitable connectors

Seite / page






USK-M/P 8. 20 IP 54



LKI-M/P 8. 21 IP 54



US-M/P 8. 3-8 IP 54

FLEXA No.	AD OD				
grau grey	Ø	mm	mm	kg/m	m
2030.101.007	10	7,0 x 10,0	8	0,070	50
2030.101.010*	14	10,0 x 14,0	10	0,085	50
2030.101.013*	17	13,0 x 17,0	13	0,130	50
2030.101.015*	19	15,0 x 19,0	15	0,150	50
2030.101.016*	21	16,0 x 21,0	17	0,210	50
2030.101.021	27	22,0 x 27,0	20	0,290	50
2030.101.029	36	29,0 x 36,0	25	0,440	25
2030.101.038	45	38,0 x 45,0	36	0,542	25
2030.101.048	56	48,0 x 56,0	40	0,875	25
Verkaufsverpackung 10 m 10 m sales pack					** in Ringen ** in rings
2031.101.007	10	7,0 x 10,0	8	0,070	10
2031.101.010*	14	10,0 x 14,0	10	0,085	10
2031.101.013*	17	13,0 x 17,0	13	0,130	10
2031.101.015*	19	15,0 x 19,0	15	0,150	10
2031.101.016*	21	16,0 x 21,0	17	0,210	10
2031.101.021	27	22,0 x 27,0	20	0,290	10
2031.101.029	36	29,0 x 36,0	25	0,440	10
2031.101.038	45	38,0 x 45,0	36	0,542	10**
2031.101.048	56	48,0 x 56,0	40	0,875	10**

* mit NEMKO-Approbation
* with NEMKO approval

Andere Abmessungen auf Anfrage
Further dimensions on inquiry