

Han INOX 10B-HTE-R-M32



| | |
|--------------------|---|
| Part number | 19 44 310 0447 |
| Specification | Han INOX 10B-HTE-R-M32 |
| HARTING eCatalogue | https://b2b.harting.com/19443100447 |

Identification

| | |
|--------------------------|----------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-INOX® |
| Type of hood/housing | Hoods |

Version

| | |
|----------------------|---------------------------------------|
| Locking type | Single locking lever |
| Size | 10 B |
| Version | Top entry |
| Cable gland | 1x M32 |
| Field of application | Hoods/housings for harsh environments |

Technical characteristics

| | |
|--|-----------------|
| Limiting temperature | -40 ... +125 °C |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-----------------------------|-----------------|
| Material (hood/housing) | Stainless steel |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | No |
| REACH ANNEX XIV substances | No |
| REACH SVHC substances | No |



Pushing Performance

Specifications and approvals

| | |
|-----------|--|
| Approvals | DNV GL |
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |

Commercial data

| | |
|-----------------------|----------|
| Packaging size | 1 |
| Net weight | 818 g |
| Country of origin | Germany |
| Customs tariff number | 85389099 |