


DIGITAL MULTIMETER

KPS-MT30



- Digital multimeter
- 2000 accounts
- AC / DC voltage, DC current and resistance measurements
- Continuity warning and diode test
- Hold readings on screen
- Low battery indication
- CAT.III 600V according to EN 61010



KPS-MT30

DIGITAL MULTIMETER

General	
Power Supply	1×9V 6F22 NEDA 1604 Battery
Product Size	145mm×76mm×40mm
Product Weight	202g
Certificate	CE/ETL/RoHS
Safety Rating	CAT III 600V

Specs	
Display Counts	2000
Diode	3.0V
Continuity Buzzer (<70 ±30Ω)	✓
Data Hold	✓

KPS-MT30

DIGITAL MULTIMETER

Specs	Range	Resolution	Accuracy
DC Voltage	200mV/2V/20V/200V	0.1mV/1mV/10mV/0.1V	±(0.5%+3)
	600V	1V	±(0.8%+5)
AC Voltage	200V/600V	0.1V/1V	±(1.2%+10)
DC Current	20µA	0.01µA	±(1.0%+3)
	200µA/2mA	0.1µA/1µA	±(1.0%+3)
	20mA	10µA	±(1.0%+5)
	200mA	0.1mA	±(1.5%+5)
	10A	10mA	±(3.0%+10)
Resistance	200Ω	0.1Ω	±(0.8%+5)
	2kΩ/20kΩ/200kΩ	1Ω/10Ω/0.1kΩ	±(0.8%+5)
	2MΩ	1kΩ	±(0.8%+5)

Product Code Information

SKU	KPSMT30CBINT
EAN code	8435394710228
UPC code	810053673560
Pcs/export carton	20