


Specification sheet: SP-DSR-117

Firm : Distrelec Schweiz AG TBS partnumber : **SP-DSR-117**Address : Grabenstrasse 6 Date : 3-8-2020

Zip / City : 8606 NÄNIKON Your partnumber : 30180804
Customercode : 13996215 / DSR

Coiled cable dimensions



Weight: ± 0,18 kg/pc

Cable specification

Cable type : LiF12Y11Y 6x0,25 mm² TB45 FLEX Stranding : 32x0,10 mm bare copper wires

Conductor insulation : TPE-E

Conductor colours : according to DIN 47100

Overall sheath : PUR

Colour : black (glossy)
Temperature range : -25 °C to +70 °C



Photographs are for illustrative purposes only

Tolerances ± 10% (dimensions and quantities)

Attention: Coiled cables, power cords and (cable) assemblies are customized products, specifically manufactured and supplied upon order. Therefore these products cannot be returned or exchanged in any way. Offer is non-committal, fixed price for up to 6 weeks, subjected to prior sale, subjected to technical changes, especially changes in measurement and construction. All our offers, orders granted to us and (project) contracts/agreements with us are subjected to the METAALUNIE TERMS AND CONDITIONS only.

These terms and conditions have been filed at the Registry of the Rotterdam District Court.

TBS de Buck B.V. De Slof 2 5107 RJ Dongen The Netherlands V.A.T.-nr.: NL 8059.10.888.B01

HR Eindhoven nr.: Rabobank Tilburg nr.: IBAN code : BIC code : 18048791 0304.1314.07 NL39 RABO 0304 1314 07 RABONL2U Phone : +31 (0) 162 523 436
E-mail : sales@the-best-solution.com
Internet : www.the-best-solution.com