


DESTB-1002

2 Pole steatite ceramic high temperature blocks terminal 57a 750v



Product Image
Not Available



SPECIFICATION

Number of poles	2
Body material	Steatite
Colour	White
Min conductor size (Sq mm)	2.5
Max conductor size (Sq mm)	10
Min conductor size AWG	22
Max conductor size AWG	8
Max current (A)	57
Max voltage (V)	750
Minimum temp rating °C	-40
Max temp rating °C	200
Pitch (mm)	18.5
Height (mm)	21
Width (mm)	22
Length (mm)	24
Comments	M4 conductor clamping screws, maximum torque=1.2Nm

