


## 105990072 Datasheet

### Specifications:

Item	Value
Operating Voltage	5V
Phase	4
Reduction ratio	1/64
Step Angle	5.625 °/64
Diameter	28mm / Nema 11
Idle In-traction Frequency	>500HZ
Idle Out-traction Frequency	>1000HZ
Resistance	21 ±7%
Noise	≤40dB
Drive mode	four-phase eight-stepping



- 1 IN1: input 1 connect to phrase 1
- 2 IN2: input 2 connect to phrase 2
- 3 IN3: input 3 connect to phrase 3
- 4 IN4: input 4 connect to phrase 4
- 5 GND: connect this module to the system GND
- 6 VCC: we use 5v for this module
- 7 VM: optional power for Motor

- A connect D4 to Blue coil
- B connect D3 to Pink coil
- C connect D2 to Yellow coil
- D connect D1 to Orange coil
- E Connect Power switch pin to Red coil

