





Product may differ from Image

### Utilization category

AC-1	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)
DC-13	3 A (24 V DC); 0.22 A (110 V DC); 0.1 A (230 V DC)

### Input

Connection voltage - current	24 VAC/DC (21.6...28 VAC/DC) - 38mA
LED display	LED (green)

### General data

Mech./ elect. life	10.000.000 switching cycles/load dependent
Test isolation voltage	4 kV
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Temperature range	-20...+50 °C
Dimensions H × W × D	86×22.5×62 mm

### Output

Switching voltage	max. 250 V AC/DC
Switching current per output	max. 6 A
Min. load current	10 mA
Power rating (voltage dependent)	max. 1500 VA/100 W
Switching frequency	max. 5 Hz
Contact material	Ag Ni 10 hv
Energize/release/contact bounce time	15/15/1.5 ms

### Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1