


## POTENTIAL TERMINAL BLOCK GRAY GRAY BR BL

Potential terminal block  
gray/gray/brown/blue


### [Link to Product](#)

#### Illustration



Product may differ from Image

#### Approvals



#### Technical Data

Operating voltage	max. 30 V AC/DC
Total current	max. 10 A

#### General data

Protection	IP20
Connection	Spring clamp terminals: 0.08...2.5 mm <sup>2</sup> (AWG 28...12)
Dimensions H × W × D	70×56×32.5 mm

Temperature range 0...+55 °C (storage temperature -40...+85 °C)

**Commercial data**

country of origin DE

customs tariff number 85369010

minimum order quantity 1