



Model Number


V93-G

Female connector, 7/8" - 16 UN2B, 3-pin, field attachable

Features

- Screw terminal connection
- Internal connector thread
- Gold plated contacts

Dimensions



Technical data

General specifications

Number of pins	3
Connection 1	socket
Construction type 1	straight
Threading 1	7/8"

Electrical specifications

Operating voltage	U_B	max. 600 V
Operating current		max. 18 A
Volume resistance		< 5 m Ω

Ambient conditions

Ambient temperature	-40 ... 90 °C (-40 ... 194 °F)
---------------------	--------------------------------

Mechanical specifications

Degree of protection	IP67
Connection	1 x 7/8" - 16 UN2B ; Socket, straight , screw terminal for 14 - 22 AWG

Material

Contacts	gold plated Cu alloy
Body	Polyamide (PA)
Slotted nut	black anodized aluminum
Sleeve connector	yellow PVC

Cable

Sheath diameter	5 ... 13 mm
-----------------	-------------

Approvals and certificates

UL approval	cULus Listed, General Purpose
-------------	-------------------------------

Electrical connection

