

TB Davies Mobile Safety Step (Punched)



[Representative image of product]

Product Description

Kitemarked and tested by BSI to EN131-7, these steps are constructed from strong tubular mild steel with double handrail, toe-boarded platform and enclosed guardrail for assured working and stock picking in commercial environments. Available in a range of sizes with an all-metal punched tread for maximum grip.

Features

- Large 560 x 400mm top platform tread to comfortably work from
- Locking device and anti-ascent bar
- Please note 10 tread & above supplied in 2 parts
- Easy one user manoeuvrability on 4 x rolling wheels
- Optional extras available for full customisation
- Not suitable for outdoor use

Product Dimensions

SKU	Treads	Platform Height	Approx. Working Height ¹ (mm)	Height (mm)	Width (mm)	Depth (mm)	Nett Weight (kg)
2017-003	3	750	2350	1750	860	810	28.0
2017-004	4	1000	2600	2000	905	965	32.0
2017-005	5	1250	2850	2250	950	1120	55.0
2017-006	6	1500	3100	2500	995	1275	62.0
2017-007	7	1750	3350	2750	1040	1430	70.0
2017-008	8	2000	3600	3000	1085	1585	78.0
2017-009	9	2250	3850	3250	1130	1740	90.0
2017-010	10	2500	4100	3500	1175	1895	98.0
2017-011	11	2750	4350	3750	1220	2050	106.0
2017-012	12	3000	4600	4000	1265	2205	116.0
2017-013	13	3250	4850	4250	1310	2360	122.0
2017-014	14	3500	5100	4500	1355	2515	130.0
2017-015	15	3750	5350	4750	1400	2670	138.0

¹ Working height is calculated as 1,600mm plus platform height or last climbing tread, whichever is appropriate. Ladders set at an angle of 75° degrees. Note that 10 tread and above are supplied in 2 sections, which require bolting together before first use.

Specifications

- Warranty: 1-year
- Standard: EN131-7
- Material: Steel
- Commodity Code: 73269030
- Country of Origin: GB
- Recommended Usage: Intensive

Common Dimensions

- Rung Depth: 180mm
- Distance Between Rungs: 210mm
- Handrail Height: 950mm

Availability & Delivery

Non-stock item. Delivery up to 14 days.
 (See exceptions, if applicable, overleaf)

Shipping Dimensions

SKU	Barcode	Shipping Length (mm)	Shipping Width (mm)	Shipping Depth (mm)	Shipping Volume (m ³)	Gross Weight (kg)
2017-003	5060169481046	1750	810	860	1.219	28.0
2017-004	5060169481053	2000	965	905	1.747	32.0
2017-005	5060169481060	2250	1120	950	2.394	55.0
2017-006	5060169481077	2500	1275	995	3.172	62.0
2017-007	5060169481084	2750	1430	1040	4.09	70.0
2017-008	5060169481091	3000	1585	1085	5.159	78.0
2017-009	5060169481107	3250	1740	1130	6.39	90.0
2017-010	5060169481114	3500	1895	1175	7.793	98.0
2017-011	5060169481121	3750	2050	1220	9.379	106.0
2017-012	5060169481138	4000	2205	1265	11.157	116.0
2017-013	5060169481145	4250	2360	1310	13.139	122.0
2017-014	5060169481152	4500	2515	1355	15.335	130.0
2017-015	5060169481169	4750	2670	1400	17.756	138.0

Please note that products marked '**Special Order**' cannot be cancelled and are non-returnable once orders are acknowledged and placed.
 This document is presented as a guide only; It is subject to change without notice and as such is not legally binding, nor does it form part of any contract.