

## Product information

# 97 52 06 SB

## Crimping Pliers

For two-hand operation




- For solder-free electrical connections
- The ingenious lever transmission reduces the handforce up to 30% compared with regular crimping pliers
- Consistently high crimping quality thanks to precision dies and ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Two-hand operation for easy crimping of large conductor diameters
- Easy handling as a result of well balanced centre of gravity, angled head and ergonomically shaped handles
- Special quality chrome vanadium electric steel, oil-hardened


### General

Article No.	97 52 06 SB
EAN	4003773039464
Pliers	burnished
Head	burnished
Handles	with non-slip plastic grips
Weight	587 g
Dimensions	250 x 115 x 30 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

### Technical details

	
Application	insulated terminals, plug connectors + butt connectors
Capacity in square millimetres	0.5 — 6 mm <sup>2</sup>
Number of crimping positions	3
AWG	20 — 10

*technical change and errors excepted*



Third step: when greater hand force is required, such as e.g. when crimping insulated connectors 6.0 mm<sup>2</sup>, two-hand operation is possible by the longer handles

Second step: now use the whole hand for further crimping procedure



First step: move the handle with two fingers only until both jaws touch the connector to be crimped