

## Product information

**98 00 19**

- Jaw 15° angled
- Basic tool chrome-plated
- Chrome vanadium steel, forged, oil-hardened

## Open-end wrench

IEC 60900 DIN EN 60900




⚡ 1000 V ♻️

### General

Article No.	98 00 19
EAN	4003773019992
Weight	154 g
Dimensions	44 x 15 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Width across flats	19 mm
Length l max.	165 mm
Head thickness a max.	9 mm
Head width b max. mm	47 mm



*technical change and errors excepted*

