


INTERCONNECTION

Pluggable Terminal Strips Plug in Style

- Moulded in white UL94-V2 self extinguishing PA6
- Easily cut to size
- IMQ, CE Approved
- UL94-VO (160°C) flame retardant version available on request.
- Available pre-cut to length



SPECIFICATION




Voltage (max)	450V AC
Working temperature	85°C
Short period	85°C
No. of poles	12
Moulding	UL94-V2 Self extinguishing PA 6
Conducting bush	Brass
Screws	Zinc, colour passivated and tropicalised

TYPE NO.	SIZE / RATING	INSERT DIAMETER	TERMINAL SCREWS	LENGTH	WIDTH	HEIGHT	PITCH	FIXING HOLE DIAMETER	MAX CURRENT
CTSN431/12MF	8mm/6A	2.9mm	M3	94.8mm	16mm	15.3mm	8mm	2.5mm	17.5A
CTSN433/12MF	10mm/10A	3.4mm	M3	119mm	20.3mm	16.4mm	10mm	3.2mm	24A
CTSN434/12MF	12mm/16A	4.3mm	M3.5	141.9mm	23.2mm	19.2mm	12mm	3.3mm	57A


Strain relief

- Clamps external conductors in lighting fixtures according to EN 60598
- Natural colour PA6
- Takes the strain on the wires
- Prevents conductors from twisting
- Protects wire coating from abrasion and friction

CSR



TYPE NO.	TERMINAL STRIP	LENGTH	WIDTH	HEIGHT
CSR1	CTSN431	49.5mm	31mm	22.5mm
CSR2	CTSN433 / CTSN433T	52.5mm	31mm	22.5mm
CSR3	CTSN434	54.5mm	31mm	22.5mm



PCB
TERMINAL
BLOCKS

INTER-
CONNECTION

FUSES &
FUSE-
HOLDERS

LEDS &
INDICATORS

MINIATURE
SWITCHES

LIMIT &
SAFETY
SWITCHES

CONTROL
PRODUCTS

INTERFACE
MODULES &
SUPPORTS

RELAY
BASES

ENCLOSURES

BATTERIES

TRANS-
FORMERS