

Analytical scales ALJ



Application:


Compact dimensions, advantageous in limited space

Execution:

- Fast and efficient working thanks to the graphic display. Simple plain text user guidance in the display in languages DE, GB, FR, IT, ES, PT
- CAL calibration program for setting accuracy. External test weights are required for this (not included in scope of delivery)
- Short settling time: Stable weighing values within approx. 6 | 10 s
- Weighing with tolerance range (checkweighing): Input of an upper/lower limit. An optical and acoustic signal supports portioning, dosing and sorting
- Dosing aid: High-efficiency mode and other filter settings can be selected
- Internal memory for complete recipes with name and setpoint of the recipe components. Display-supported user guidance
- Ergonomically optimised control panel for left- and right-handed users
- Large glass wind guard with 3 sliding doors for convenient access to the weighing goods
- Compact dimensions, advantageous in limited space
- with a large weighing range, graphic display and convenient recipe function

Delivery:

with storm cuff, power supply unit and work protection hood



Art. no.	49000 063
Brand	KERN
Manufacturer Part Number	ALJ 250-4A
Type description	ALJ 250-4A
Max. weight measuring range	250 g
Digit increment, weight	0.0001 g
Digit height	15 mm
Plate diameter	80 mm
Material of cover panel	Stainless steel
With unit counting	Yes
Min. item weight	10 mg
Reproducibility	0.0001 g
Linearity	0.0003 g
Data transmission type	RS232
Housing dimensions (LxWxH)	210 x 340 x 330 mm
Display type	Graphic LCD
Gross Weight	9.250 kg
Product Group	447

EAN

4045761107953