

Aluminium step ladder

Accessible from both sides – wide steps

ATORN®

Application

For ensuring all work at height is reached and completed safely

Version

- High-strength extruded aluminium strut profiles in C-profile shape = light weight and maximum torsional rigidity
- Particularly deep aluminium treads allow safe, fatigue-free standing
- The joints between the stiles and the rungs use highly shear-resistant steel rivets to guarantee the highest possible level of safety and maximum durability for the aluminium ladder
- 12 sturdy aluminium cross struts ensure optimum stability of the stepladder
- Special soft plastic shoes guarantee superb resistance to displacement when standing

Advantage

- steps with 85 mm deep outlet areas



Art. No.	50259 580
Number of steps	2 x 3
Working height	1.71 m
Length	0.73 m
Platform height	0.64 m
Height, vertical	0.73 m
Pedestal width	0.43 m
Weight	4.7 kg
Accessibility	Both sides
Max. load capacity	150
Step depth	85 mm
Material	Aluminium
Folding	Yes
EN standard	131

EAN-Code

4050293568646