

Lift lever chain hoist UNOplus

Compact, robust design

Yale

Application:

For tensioning, hoisting, pulling and tying down.

Execution:

- Compact and robust sheet steel housing
- Zinc-plated load chain in line with DIN EN 818-7 (quality class T)
- Smooth-running free-chaining feature for rapid load attachment
- 360° rotating carrying hook
- Chain end made of shatter-proof plastic
- Automatic threaded mechanical brake

Advantage:

- low tare weight
- Requires low lifting power



Art. no.	77157 070
Brand	YALE
Manufacturer Part Number	2300163
Model	UNOplus 3000
Load-carrying capacity	3000 kg
Nominal chain thickness	30 mm
Chain diameter	10 mm
Stroke force at nominal load	40 daN
Length of lever	380 mm
Stroke height per lever revolution	17 mm
Lift height	1500 mm
Min. hook spacing	510 mm
Number of load chains	1 PCS
EN standard	818-7
Gross Weight	22.400 kg
Product Group	7EE

EAN

4053981988733