



PrimaVision Mini for CDM

HID-PV m PGJ5 20 / I CDM LPF 220-240V

Miniature HID electronic gear for PGJ5 CDM lamps – freeing up the boundaries of creativity and innovation in luminaire design

Product data

• General Information

Application Code	LPF
Type Version	mk1
Lamp Type	CDM
Number Of Lamps	1 piece/unit
Suitable For Outdoor Use	No
Number Of Products On MCB (16A Type B) (Nom)	48

• Operating and Electrical

Input Voltage	220 to 240 V
Input Frequency	50/60 Hz
Minimum Mains Voltage Operation (Min)	198 V
Operating Frequency (Nom)	0.10 kHz
Ignition Voltage (Max)	1.5 kV
Ignition Voltage (Min)	1.3 kV
Ignition Switch-Off Time (Nom)	25 min
Mains Voltage Performance (AC)	-10%/+6%
Mains Voltage Safety (AC)	-18%/+10%
Earth Leakage Current (Max)	0.25 mA
Inrush Current Width	0.40 ms
Constant Wattage Deviation	-3%/+3%
Power Losses (Nom)	3 W

Inrush Current Peak (Max)	30 A
---------------------------	------

• Wiring

Cable Capacity	200 pF
Output Wires Mutual (Nom)	
Cable Length From Device To Lamp	2 m
Wire Striplength	10.0-11.0 mm
Ballast Contact Wire Cross Section	0.75-2.50 mm ²
Connector Type	Insert

• System characteristics

Rated Ballast-Lamp Power	20 W
--------------------------	------

• Temperature

T-Ambient (Max)	50 °C
T-Ambient (Min)	-20 °C
T-Storage (Max)	80 °C
T-Storage (Min)	-25 °C
T-Case Lifetime (Nom)	65 °C
T-Case Maximum (Max)	75 °C

• Mechanical and Housing

Housing	/I
---------	----

PHILIPS




• Approval and Application

Active Temperature Protection	Yes
EMI 9 kHz ... 300MHz	CISPR 15 ed 7.2
Vibration Standard	IEC 68-2-6 Fc
Bumps Standard	IEC 68-2-29 Eb
Approval Marks	F-Marking CE marking CB Certificate
Hum And Noise Level	Inaudible

• Product Data

Full product code	871150090981730
Order product name	HID-PV m PGJ5 20 /I CDM LPF 220-240V
EAN/UPC - Product	8711500909817
Order code	913700601666
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material Nr. (12NC)	913700601666
Net Weight (Piece)	0.140 kg

Dimensional drawing



HID-PV m 20 /GMI CDM HPF

HID-PV m PGJ5 20 /I CDM LPF 220-240V

Product	D1	C1	A1	A2	B1
HID-PV m PGJ5 20 /I CDM LPF 220-240V	4.2 mm	30.0 mm	190.0 mm	154.0 mm	43.3 mm



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, December 24
data subject to change