

NYLONDÜBEL

Nylon



Art.-Nr.	D (mm)	Details	Inhalt (Stück)	Mindestmenge (Karton)	VE (Karton)	EAN
905 5 65	5,0	Bohr-Ø 5 mm	100	3	1	4009155299624
905 6 65	6,0	Bohr-Ø 6 mm	100	3	1	4009155299631
905 8 65	8,0	Bohr-Ø 8 mm	100	3	1	4009155299648
905 10 65	10,0	Bohr-Ø 10 mm	50	3	1	4009155293950
905 12 65	12,0	Bohr-Ø 12 mm	25	3	1	4009155293967
905 14 65	14,0	Bohr-Ø 14 mm	20	3	1	4009155636290
905 16 65	16,0	Bohr-Ø 16 mm	10	3	1	4009155652351

HOHLRAUMDÜBEL

mit Kappe

Polyethylen



Art.-Nr.	D x L (mm)	Details	Inhalt (Stück)	Mindestmenge (Karton)	VE (Karton)	EAN
906 06 37 65	6,0 x 34	Bohr-Ø 6 mm	50	3	1	4009155348766
906 08 52 65	8,0 x 47	Bohr-Ø 8 mm	50	3	1	4009155348773
906 010 62 65	10,0 x 57	Bohr-Ø 10 mm	50	3	1	4009155348780
906 012 72 65	12,0 x 68	Bohr-Ø 12 mm	25	1	1	4009155739854
906 014 75 65	14,0 x 73	Bohr-Ø 14 mm	25	1	1	4009155739861