


# E10136



## Wirable socket

SDOGH042PLSFKPG



### Electrical data

Operating voltage [M] 10...30 DC

### Outputs

Electrical design PNP

### Operating conditions

Ambient temperature [°C] -40...85

Protection IP 67

### Mechanical data

Weight [g] 14.8

Dimensions [mm] 18 x 18 x 46

Materials PA

Material nut PA

### Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

### Remarks

Pack quantity 1 pcs.

### Electrical connection

screw terminals: ...0.75 mm<sup>2</sup>; Cable sheath: Ø 4...6 mm


### Electrical connection - socket

Connector: 1 x M12, straight; Moulded body: PA; Locking: PA

# E10136

## Wirable socket

SDOGH042PLSFKPG



### Connection

