



Datenblatt - Fiche technique - Data sheet


**11.04.5506**



ROLINE GOLD HDMI High Speed Kabel mit Ethernet, 10,0m


ROLINE GOLD Câble HDMI High Speed avec Ethernet, M-M, 10,0m

ROLINE GOLD HDMI High Speed Cable + Ethernet, M/M, 10 m



**Electrical Test:**

1. 100%Test(Open ,short ,miss wire)
2. Contact Resistance: 5 ohm max.
3. Insulation Resistance: 10M ohm min.
4. Hi-pot:300V DC/10ms



|     |   |       |      |
|-----|---|-------|------|
| 11  | Wire Clip OD:7.3mm  | 2     | pcs  |
| 10  | TUBE BLACK #1.5mm THIN  | 0.032 | m    |
| 9   | HDMI 20# BALCK ABS JACKET   | 2     | pcs  |
| 8   | HDMI M TRANSPARENT DUST COVER   | 2     | pcs  |
| 7   | 45P BLACK PVC   | 16    | g    |
| 6   | TRANSPARENT PE  | 3     | g    |
| 5   | TUBE BALCK #0.8mm THIN.   | 0.024 | m    |
| 4   | TUBE BALCK #2.0mm THIN.   | 0.08  | m    |
| 3   | HDMI 20# Shell aluminium alloy laser etching HDMI LOGO                              | 2     | pcs  |
| 2   | HDMI M SOLDER TYPE,GOLD PLATED SHELL , BLACK INSULATION                             | 2     | pcs  |
| 1   | (28#*1P+EAM)*5PCS+28#*4C+AL+7/0.127TC+80/0.12ALM(50%)OD:7.3mm WITH BLACK/YELLOW NET | 10    | M    |
| NO. | DESCRIPTION   | Q'TY  | UNIT |

| TOLERANCE |        |     |
|-----------|--------|-----|
|           | INCHES | M/M |
| .X        | .015   | .30 |
| .XX       | .010   | .10 |
| .XXX      | .005   | .05 |

**rotronic**

11.04.5506

ROLINE GOLD HDMI Cable, w/Ethernet, A M / A M  
10m, black w/yellow & black nylon net

DRAWN BY

CHECK BY

APPD BY

SCALE

NONE

UNIT

MM

DATE

2013.07.26

DRAWING NO.:

REV.

A

1/1