



6W

VT-826 6W LED WALL LIGHT COLORCODE:4000K -WHITE BODY

| | | |
|----------------------|--------------------------|----------------------------------|
| Lumens 660 | Beam Angle 120 | Dimensions 90x200x90mm |
|----------------------|--------------------------|----------------------------------|

Day White
SKU:8296

2 YEARS
WARRANTY

SENSOR
COMPATIBLE



Technical Information

| | | | |
|----------------|--------------|------------------------|---------------------|
| Watts: | 6 | Dimmable: | No |
| Lumens: | 660 | Warranty (Years): | 2 |
| Beam Angle: | 120 | PF: | >0.5 |
| Unit Color: | White | CRI: | >80 |
| Body Type: | Aluminium | Operation Temperature: | -20°C to +45°C |
| Long life: | 20,000 Hours | Input Power: | AC:220-240V,50/60Hz |
| LED Chip Type: | SMD | Sensor Compatibility: | Yes |
| IP Rating: | IP65 | | |

Features

- ✓ High Quality Bridgelux chips for reliable operation and lifetime
- ✓ Get range of up-down beams with Adjustable beam angle to feel range of aesthetics
- ✓ Constructed to high quality aluminum for efficient heat dissipation
- ✓ Cylindrical & Cubical fixtures in 3 colors to fit into range of architectural structures
- ✓ Elegant replacement for traditional up-down lighting
- ✓ Application: Perfect for living rooms, pathways, balconies, facades etc

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs 0.95

Unit CBM 0.00304175

Master Box Packaging

Master Box Qty (Pcs Per Carton) 20

Qty Per Pallet 480

Listing Details

EAN Code 3800157629904

Commodity Code 9405403990

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER

70

COUNTRIES