

## Mini Continuum II - Direct/Indirect - Suspended Kit


### MC2-KIT D/I 2.4M 3K DALI WHT PRIS

### 2093111



#### Product features

- 2093111 MC2-KIT D/I 2.4M 3K DALI WHT PRIS Continuous lines of LED light, white RAL 9016, direct/indirect distribution (65/35), suspended kit version is pre-wired and supplied complete with end caps and suspension cables, compact and minimalist design based on the Golden Mean, ideal for offices, meeting rooms, corridors, education facilities, museums and libraries, extruded aluminium body, diffuser: micro prismatic, colour temperature: 3000K warm white, total system power: 64W, total fixture output: 7400lm, luminaire efficacy: 116lm/W, LOR: 100%, colour rendering: Ra >80, LED Chromacity: 3 step MacAdam ellipse, lifespan: 66,000 hours L90B10, IR/UV free light source without heat radiation, operating voltage: 220-240V / 50-60Hz, drive current: (Direct) 800mA + (Indirect) 350mA, electronic driver, DALI dimmable, direct/indirect independently addressable, electrical protection: CLASS I, IP20, suitable for internal environment only.



#### PRODUCT OVERVIEW

Product name	MC2-KIT D/I 2.4M 3K DALI WHT PRIS
Technology	LED
Housing	Aluminium
Mount	Suspended
Environment	Internal
General application	Education, Hospitality, Office, Retail
ETIM Class	EC001743
E-number FI	4237819
Warranty	5 years
Fixture luminous flux (lm)	7400
Luminaire efficacy (lm/W)	116
LOR (%)	100
Colour temperature (K)	3000
Light colour	Warm White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Glare control	< 19
Photobiological Risk Group	RG0
Total power consumption (W)	64
Electrical protection	Class I
Control gear type	Electronic ballast
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768931118

## Mini Continuum II - Direct/Indirect - Suspended Kit

*MC2-KIT D/I 2.4M 3K DALI WHT PRIS*  
2093111

### DATA TABLE

#### General data

<b>Product name</b>	MC2-KIT D/I 2.4M 3K DALI WHT PRIS
<b>Technology</b>	LED
<b>Housing</b>	Aluminium
<b>Mount</b>	Suspended
<b>Environment</b>	Internal
<b>General application</b>	Education, Hospitality, Office, Retail
<b>Performance ambient temperature Tq (°C)</b>	25
<b>ETIM Class</b>	EC001743
<b>E-number FI</b>	4237819
<b>Warranty</b>	5 years

#### Optical data

<b>Fixture luminous flux (lm)</b>	7400
<b>Luminaire efficacy (lm/W)</b>	116
<b>LOR (%)</b>	100
<b>Colour temperature (K)</b>	3000
<b>Light colour</b>	Warm White
<b>CRI (Ra)</b>	80
<b>Colour Variation Initial (SDCM)</b>	SDCM3
<b>Adjustable chromaticity</b>	N
<b>Glare control</b>	< 19
<b>Photobiological Risk Group</b>	RG0

#### Electrical data

<b>Total power consumption (W)</b>	64
<b>Mains voltage (V)</b>	220-240V
<b>Lamp power factor</b>	0.95
<b>Electrical protection</b>	Class I
<b>Control gear type</b>	Electronic ballast
<b>Transformer required</b>	Yes
<b>Dimming method</b>	DALI
<b>Minimum dimming level (%)</b>	1
<b>Drive current (mA)</b>	800
<b>Inrush Current (A)</b>	30
<b>Inrush Duration (µs)</b>	200
<b>Energy Efficiency Class (A-&gt;G) of contained light source</b>	C
<b>Max. Luminaires per 16A C Breaker</b>	48

#### Lifetime data

<b>Lifespan L70 B50</b>	120000
<b>Lifespan L80 B20</b>	120000
<b>Lifespan L90 B10</b>	66000

## Mini Continuum II - Direct/Indirect - Suspended Kit MC2-KIT D/I 2.4M 3K DALI WHT PRIS 2093111





### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	2400
Nominal Product Width (mm)	54
Nominal Product Height (mm)	86
Weight (kg)	6.5

### Packaging

Single packaging type	Carton
Product EAN number	5025768931118
Packaging single length / height (cm)	254.0
Packaging single width (cm)	15.0
Packaging single depth (cm)	15.0
DUN14 (outer)	05025768931118
Units per outer package	1
Packaging outer length / height (cm)	254.0
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	15.0

## PHOTOMETRY



## Mini Continuum II - Direct/Indirect - Suspended Kit

*MC2-KIT D/I 2.4M 3K DALI WHT PRIS*  
2093111

### TECHNICAL DRAWINGS

