

Metal circular saw blade, HSS, coarse-toothed, type B

for universal use up to 1000 N/mm² in larger cross sections and cutting depths on conventional machines

ORION[®]

Application:


For making saw cuts in large cross-sections and for medium to deep cutting depths in the material groups of steel, (stainless steel), cast iron and (non-ferrous metals).

Execution:

- precision-ground metal circular saw blade with tooth type B, coarse serrated, laterally hollow ground and hole without keyway

Advantage:

- innovative cutting geometry with large chip space ensures chip removal and universal application
- top-quality cutting material for extremely demanding requirements in terms of service life
- universal use for a multitude of applications



Art. no.	14004 470
Brand	ORION
Manufacturer Part Number	14004470
Tooth shape	B
Cutting material	HSS
Thickness of cutting edge	2 mm
Tolerance of cutting edge diameter	js 15
Tolerance of cutting edge thickness	js 11
Tolerance of hole diameter	H7
Cutting edge diameter	125 mm
Bore diameter	22 mm
Number of teeth	64 PCS
DIN	1838
Gross Weight	0.180 kg
Product Group	1QK

EAN

4039247079766