

Pocket multimeter MMP3

Small digital multimeter in leather case

BENNING

Application:

For use in installation fields and simple, industrial fields.

Delivery:

Includes leather case, batteries, permanently connected measuring leads



Art. no.	75021 200
Brand	BENNING
Manufacturer Part Number	044084
Model	MM P3
Display range	5000 digits
Measuring accuracy	+/- 0.6 %
Min./max. test voltage (DC)	100 μ V/DC-600 V/DC
Min./max. test voltage (AC)	100 μ V/AC-600 V/AC
Continuity testing	Yes
Diode testing	Yes
Min./max. electrical-resistance measuring range	0.1 Ohm-40 MOhm
Min./max. frequency	0.000000001 / 5 MHz
Volt sensor	No
Memory function	HOLD
Measuring procedure	RMS
Overvoltage protection category	CAT III/300 V
Length x width x height	132 x 86 x 19 mm
EN standard	61010
Gross Weight	0.260 kg
Product Group	7AH

EAN

4014650440846