



Coding style table	
	Style A: For connectors 6 poles
	Style B: For connectors 10 and 14 poles
	Style C: For connectors from 16 to 64 poles



-Technical information available on a separate document ref: DS 09181100001
-Full range of P/N's and dimensions shown on page 2/2

	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN	Date 2014-05-16	State Final Release	Ref. Sub.
	HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 18 male straight low profile			Doc-Key / ECM-Nr. 100565935/UGD/001/A 50000068837		Rev. A
		Type TB	Number 09185XXX324		Page 1/2		

Performance Level				Dimensions			
	PL3	PL2	S4				
Nb of Contacts	Part Number	Part Number	Part Number	Insulator Color	A Max	B	E
06	0918 506 7324	0918 506 6324	0918 506 5324	Grey	15,4	12,78	2,54 x 2 = 5,08
10	0918 510 7324	0918 510 6324	0918 510 5324		20,5	17,86	2,54 x 4 = 10,16
14	0918 514 7324	0918 514 6324	0918 514 5324		25,6	22,94	2,54 x 6 = 15,24
16	0918 516 7324	0918 516 6324	0918 516 5324		28,1	25,48	2,54 x 7 = 17,78
20	0918 520 7324	0918 520 6324	0918 520 5324		33,2	30,56	2,54 x 9 = 22,86
26	0918 526 7324	0918 526 6324	0918 526 5324		40,8	38,18	2,54 x 12 = 30,48
30	0918 530 7324	0918 530 6324	0918 530 5324		45,9	43,26	2,54 x 14 = 35,56
34	0918 534 7324	0918 534 6324	0918 534 5324		51,0	48,34	2,54 x 16 = 40,64
40	0918 540 7324	0918 540 6324	0918 540 5324		58,6	55,96	2,54 x 19 = 48,26
50	0918 550 7324	0918 550 6324	0918 550 5324		71,5	68,66	2,54 x 24 = 60,96
60	0918 560 7324	0918 560 6324	0918 560 5324		84,2	81,36	2,54 x 29 = 73,66
64	0918 564 7324	0918 564 6324	0918 564 5324		89,3	86,44	2,54 x 31 = 78,74
06	0918 506 7324 001	0918 506 6324 001	0918 506 5324 001		Black	15,4	12,78
10	0918 510 7324 001	0918 510 6324 001	0918 510 5324 001	20,5		17,86	2,54 x 4 = 10,16
14	0918 514 7324 001	0918 514 6324 001	0918 514 5324 001	25,6		22,94	2,54 x 6 = 15,24
16	0918 516 7324 001	0918 516 6324 001	0918 516 5324 001	28,1		25,48	2,54 x 7 = 17,78
20	0918 520 7324 001	0918 520 6324 001	0918 520 5324 001	33,2		30,56	2,54 x 9 = 22,86
26	0918 526 7324 001	0918 526 6324 001	0918 526 5324 001	40,8		38,18	2,54 x 12 = 30,48
30	0918 530 7324 001	0918 530 6324 001	0918 530 5324 001	45,9		43,26	2,54 x 14 = 35,56
34	0918 534 7324 001	0918 534 6324 001	0918 534 5324 001	51,0		48,34	2,54 x 16 = 40,64
40	0918 540 7324 001	0918 540 6324 001	0918 540 5324 001	58,6		55,96	2,54 x 19 = 48,26
50	0918 550 7324 001	0918 550 6324 001	0918 550 5324 001	71,5		68,66	2,54 x 24 = 60,96
60	0918 560 7324 001	0918 560 6324 001	0918 560 5324 001	84,2		81,36	2,54 x 29 = 73,66
64	0918 564 7324 001	0918 564 6324 001	0918 564 5324 001	89,3		86,44	2,54 x 31 = 78,74

	All Dimensions in mm Original Size DIN A3	Scale 1:1	Free size tol.	Ref.
	All rights reserved Department EC PD - FR	Created by DOUGE	Inspected by BAGDIKIAN	Standardisation HOFFMANN
HARTING Electronics GmbH D-32339 Espelkamp	Title SEK 18 male straight low profile			Doc-Key / ECM-Nr. 100565935/UGD/001/A 50000068837
	Type TB	Number 09185XXX324	Rev. A	Page 2/2