

2A3B/2A3C

$U_f=2.5V$ 。

Maximum Rating

U_a -----400 V

P_a -----25 W

Static Parameter

U_a -----300 V

$-U_g$ -----45 V

I_a -----60 mA

G_m -----5.25 mA/V

r_i -----0.8 k Ω

μ -----4.2

P_{out} -----3.5 W

Characteristic Curve

