



## MASI20 INSTALLATION TECHNOLOGY


Distributor 2x AS-I and 3x extern power

2 AS-Interface + 3 power ports  
potentially separated  
5 plug terminals included

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Technical Data

Operating voltage	max. 36 V DC
Current per connection	max. 8 A
Total current	max. 24 A
Isolation voltage	AS-Interface/Power 200 V, (EN 60664-1)

### General data

Protection	IP20
Connection	Screw terminal: single wire (0.25...4 mm <sup>2</sup> ), stranded wire (0.5...2.5 mm <sup>2</sup> )
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-20...+70 °C (storage temperature -40...+80 °C)
Dimensions H × W × D	52×67×90 mm

### Commercial data

country of origin	CZ
customs tariff number	85176200
minimum order quantity	1