



## T-COUPLER SLIMLINE M12 MALE / 2X M8 FEMALE


T-coupler (Slimline) M12 - M8  
4-pole  
Distribution function (NO)

Plastic housings with good resistance against chemicals and oils. The resistance to aggressive media should be individually tested for your application. Further details on request.

### [Link to Product](#)

#### Illustration





Product may differ from Image

### Approvals



### Form

41211

### Technical Data

Operating voltage	max. 60 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8/M12 × 1 mm (recommended torque 0.4/0.6 Nm), self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)

### General data

Temperature range	-25...+85 °C
-------------------	--------------

### Commercial data

country of origin	DE
customs tariff number	85369010
minimum order quantity	1