



Predator Bow Saws


Razorsharp Other Cutting

A range of professional quality Bow Saws available in a variety of sizes and with spare blades for wet or dry cutting

10
YEAR
GUARANTEE

B9821 - 21" Predator Bow Saw

- 21" (530mm)
- Tension adjuster for faster, cleaner cuts for longer
- Soft feel ergonomic handle/hand guard
- Easy, rapid blade change
- Blades available for both hard wood (Peg Tooth) and soft/green wood (Raker Tooth)
Sold fitted with Peg Tooth Blade



Spare Blades
B9821WETBLADE 21" Raker Tooth Bow Saw Blade
B9821DRYBLADE 21" Raker Tooth Bow Saw Blade

B9821TF - 21" Taper Front Predator Bow Saw

- 21" (530mm)
- Ideal for use in restricted spaces
- Tension adjuster for faster, cleaner cuts for longer
- Soft feel ergonomic handle/hand guard
- Easy, rapid blade change
- Blades available for both hard wood (Peg Tooth) and soft/green wood (Raker Tooth).
Sold fitted with Peg Tooth Blade



Spare Blades
B9821WETBLADE 21" Raker Tooth Bow Saw Blade
B9821DRYBLADE 21" Raker Tooth Bow Saw Blade

B9824 - 24" Predator Bow Saw

- 24" (610mm)
- Tension adjuster for faster, cleaner cuts for longer
- Soft feel ergonomic handle/hand guard
- Easy, rapid blade change
- Blades available for both hard wood (Peg Tooth) and soft/green wood (Raker Tooth)
Sold fitted with Peg Tooth Blade



Spare Blades
B9824WETBLADE 24" Raker Tooth Bow Saw Blade
B9824DRYBLADE 24" Raker Tooth Bow Saw Blade

B9830 - 30" Predator Bow Saw

- 30" (760mm)
- Tension adjuster for faster, cleaner cuts for longer
- Soft feel ergonomic handle/hand guard
- Easy, rapid blade change
- Blades available for both hard wood (Peg Tooth) and soft/green wood (Raker Tooth)
Sold fitted with Peg Tooth Blade



Spare Blades
B9830WETBLADE 30" Raker Tooth Bow Saw Blade
B9830DRYBLADE 30" Raker Tooth Bow Saw Blade

3621K - 21" Bowsaw

- Hardpoint blade which stays sharp up to 5 times longer than untreated blades
- Teeth designed for fast and free cutting on forward and backward strokes
- Lever tension device for simple blade changing
- Angled frame for cutting in restricted areas
- 3ppi



Spare blade 3921W

3624Z - 24" Bowsaw

- Hardpoint blade which stays sharp up to 5 times longer than untreated blades
- Teeth designed for fast and free cutting on forward and backward strokes
- Lever tension device for simple blade changing
- 3ppi



Spare blade 3924C

A range of garden saws and pruning saws designed to tackle most cutting jobs in the garden

10
YEAR
GUARANTEE

4938PS - Fixed Blade Pruning Saw

- Cuts branches up to 3½"/90mm
- Ultra sharp precision ground teeth
- 9" (225mm) Carbon steel blade for durability
- Non slip ergonomic soft feel handle
- Scabbard with belt hook for safe carrying and storage



Total length 450mm

4948PS - Large Pruning Saw


- 12" (305mm) SK5 carbon steel blade for lasting sharpness
- Ultra sharp 7ppi precision ground teeth
- Chrome plated blade for rust resistance
- Blade locks in open and closed position



Blade length 305mm

4933PS - Retractable Pruning Saw

- 6" (150mm) carbon steel blade
- 6ppi teeth are hardened and tempered for strength and durability
- Retractable blade can be stored safely inside handle when not in use
- Handy belt clip



Blade length 150mm

4960RSA - Small Folding Pruning Saw

- 7" (178mm) carbon steel blade
- Hollow ground blade for enhanced cutting performance
- Ultra sharp 7ppi precision ground teeth
- Folds for storage and blade protection
- Blade locks in open and closed position



Total length 685mm

4943BE - Garden Saw

- Ideal for cutting wet (green) wood
- Fast cut, rapid, clean cutting action
- Rigid blade minimises 'whip' and vibration
- Comfortable handle - Suregrip® soft feel ergonomic grip and finger guide for accuracy, plus a 45/90° angle guide
- 7ppi



Spare blade 3921W

4950WC - Garden Wire Cutters

- SK5 Steel blades
- Clean precise cutting action eliminates frayed ends
- Cutting capacity for wire rope - Maximum 4mm
- Cutting capacity for high tensile steel - Maximum 2mm
- Cutting capacity for spring wire - Maximum 1.5mm



NEW

8200RS - Easy Reach Pruner

- Rotating body and cutting head
- Carbon steel bypass action blades for a clean cut on green stems up to 7.5mm thick
- Lightweight long handle
- PTFE coated cutting blade for easier, smooth cut
- Cut and hold mechanism for fruit/flowers

