

# Han-Snap Latching parts w. strain relief



Part number	09 33 000 9991
Specification	Han-Snap Latching parts w. strain relief
HARTING eCatalogue	https://b2b.harting.com/09330009991

Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Accessories
Series	Han-Snap <sup>®</sup>
Type of accessory	Latching parts
Description of the accessory	With strain relief

### Version

Pack contents	1 latching part with strain relief
Fack contents	1 latching part

#### Technical characteristics

Tightening torque	0.8 Nm
Limiting temperature	-40 +125 °C
Degree of protection acc. to IEC 60529	IP20
Retention force	200 N Without guiding 300 N With guiding

### Material properties

Material (accessories)	Polycarbonate (PC)
Colour (accessories)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50



## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate Lead
ECHA SCIP number	b51e5b97-eeb5-438b-8538-f1771d43c17d
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R22 (HL 1-3) R23 (HL 1-3)

# Specifications and approvals

Specifications	IEC 60068-2-6 Vibration (sinusoidal)
Specifications	IEC 60068-2-27 Shock

#### Commercial data

Packaging size	10
Net weight	19.5 g
Country of origin	Germany
European customs tariff number	85366990
GTIN	5713140050686
ETIM	EC002939
eCl@ss	27440392 Connector (accessories)