

## Myriad Deco IP65 Chrome Bezel


### MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ

#### 2058955



#### Product features

- MYRD IP ST 2.7K DALI EM BLK CBEZ



### PRODUCT OVERVIEW

Product name	MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ
Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
Warranty	5 years
Fixture luminous flux (lm)	1241
Luminaire efficacy (lm/W)	103
LOR (%)	100
Colour temperature (K)	2700
Light colour	Candlelight
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	28
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	275
Total power consumption (W)	12
Electrical protection	Class II
Control gear type	Electronic ballast
Dimming method	DALI
Minimum dimming level (%)	1
Housing colour	Black
IP rating	IP65/20
IK rating	IK02
Product EAN number	5025768589555

### DATA TABLE

#### General data

Product name	MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ
--------------	--

## Myriad Deco IP65 Chrome Bezel

*MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ*  
2058955

Technology	LED
Housing	Aluminium
Mount	Ceiling recessed mounting
Environment	Interior
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	1241
Luminaire efficacy (lm/W)	103
LOR (%)	100
Colour temperature (K)	2700
Light colour	Candlelight
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	28
Photobiological Risk Group	RG1
Luminous flux (emergency) (lm)	275
Emergency duration (h)	3

### Electrical data

Total power consumption (W)	12
Mains voltage (V)	230-240V
Electrical protection	Class II
Control gear type	Electronic ballast
Transformer required	Yes
Dimming method	DALI
Minimum dimming level (%)	1
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

### Physical data

Housing colour	Black
IP rating	IP65/20
IK rating	IK02
Diffuser finish	Bezel (or Ring)
Nominal Product Height (mm)	72
Nominal Product Diameter (mm)	90


## Myriad Deco IP65 Chrome Bezel MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ 2058955

Cutout Dimensions (W x L in mm or Diameter in mm)	76
Weight (kg)	1.44
Recessed Depth (mm)	72

### Packaging

Single packaging type	Carton
Product EAN number	5025768589555
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768589555
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

### PHOTOMETRY




### TECHNICAL DRAWINGS

## Myriad Deco IP65 Chrome Bezel

*MYRIAD DECO IP65 SPOT 2700K DALI EM BLACK CBEZ*

2058955



Dimensions (mm)