

## Spacer sleeve for MK with clamping thread (DIN 6364)

in accordance with ISO 7388-1

**ATORN**<sup>®</sup>

### Application

For holding tools with Morse taper shank in accordance with DIN 228 A with clamping thread.

### Version

- Alloyed case-hardening steel, tensile strength in the core min. 950 N/mm<sup>2</sup>
- Case-hardened HRc 60 ± 2 (HV 700 ± 50), hardness depth 0.8 mm ± 0.2 mm, bronzed
- Taper angle tolerance quality < AT3 in accordance with DIN 7187 and DIN 2080
- max. concentricity < 0.005 mm



<b>Art. no.</b>	<b>23163 041</b>
<b>Mount, on tool side</b>	MK 4
<b>Projecting length</b>	70 mm
<b>Outer diameter</b>	48 mm
<b>Tool holding device</b>	SK 50

### EAN-Code

4050293713114