

## Hydraulic pressure cylinder RC



### Execution:

- Single-acting cylinder.
- Model RC 50 with stationary thrust piece, all other cylinders with interchangeable, grooved thrust piece.
- Operating pressure of 700 bar
- With spring return mechanism.
- With scraper ring (apart from model RC 50).
- Hard-chrome-plated piston rod.
- With retaining thread on cylinder head (except mod. RC 50).

### Advantage:

- Suitable for universal use.
- Retaining ring prevents piston rod from being pushed out.

### Delivery:

1x ENERPAC hydraulic pressure cylinder RC 51.



<b>Art. no.</b>	<b>29501 050</b>
<b>Brand</b>	ENERPAC
<b>Manufacturer Part Number</b>	RC106
<b>Model</b>	RC 106
<b>Max. compressive force</b>	101 kN
<b>Lift height</b>	156 mm
<b>Oil capacity</b>	226 cm <sup>3</sup>
<b>Construction height, retracted</b>	247 mm
<b>Weight</b>	4.4 kg
<b>Gross Weight</b>	4.718 kg
<b>Product Group</b>	258