

LED workplace light Highlight

With and without dimmer



Execution:

- LED module with very low power consumption
- Streamlined shape, for universal use
- High-performance chip with lamp life of min. 50,000 operating hours
- Protected against splash water and dust, with power supply unit
- Glare- and flicker-free light, low-reflection, 160-degree uniform illumination
- 400-lumen light output, colour temperature: daylight white, approx. 5500 Kelvin
- Rubber-coated 66-mm magnetic base with adhesive force of 180 N
- Lamp head 90 x 30 x 13 mm, total length 620 mm
- Ref. no. 150: No dimmer
- Ref. no. 152: With dimmer (continuously variable)

Advantage:

- Waterproof and extremely robust
- Magnetic rubber base - prevents scratches to coated surfaces
- Made in Germany - high-quality product for demanding industrial use



Art. no.	56879 152
Brand	BAUER & BÖCKER
Manufacturer Part Number	900/42D
Power rating	2.5 W
Arm length	551 mm
IP protection class	IP 65
Dimmable	Yes
Gross Weight	0.900 kg
Product Group	5ID

EAN

4260131238062