

## Pneumatic blow-out and liquid gun MultiFLOW

320 nipple



### Application:

For cleaning work using compressed air, coolant or non-explosive water-based liquids.

### Version:

- Zinc-plated hardened steel nipple (Ø 7.6 mm)
- Precisely adjustable flow rate regulation
- Compatible with all standard pneumatic systems
- Satisfies OSHA requirements
- Planar or pointed jet with adjustable jet nozzle



<b>Art. no.</b>	<b>75103 010</b>
<b>Type</b>	320 nipple
<b>Min./max. flow capacity</b>	5-25 l/min
<b>Min. air consumption</b>	200 l/min
<b>Max. air consumption</b>	1200 l/min
<b>Min./max. air consumption</b>	200-1200 l/min
<b>Max. operating pressure</b>	16 bar
<b>Burst pressure</b>	64 bar
<b>Connection thread</b>	R 1/4 inch
<b>Min./max. sound-pressure-level</b>	79-101 dB
<b>Min./max. temperature conditions</b>	-20 to +60 °C
<b>Weight</b>	0.191 kg

### EAN-Code

7391390264039