

Pin Header DIN 41651

FEATURES:

Fully shrouded header assembly
 2.54 mm x 2.54 mm short lock
 Straight type
 Gold flash plating
 Low-lead

SPECIFICATION:

Contact material	Copper alloy, gold-plated
Connection principle	Wire-board
Gender of contacts	Male
Temperature range	-55 ... +105 °C
Pitch	2.54 mm
Housing material	PBT, UL 94V-0
Rated current	3 A
Insulation resistance	1000 MΩ min. at 1000 VDC
Dielectric voltage	1000 VAC RMS for 1 min.

Article Nr.	Contacts	Dim.A	Dim.B	Dim.C
RND 205-00802	10	32 mm	27.9 mm	10.1 mm
RND 205-00805	16	39.6 mm	35.5 mm	17.7 mm
RND 205-00808	20	44.7 mm	40.6 mm	22.8 mm
RND 205-00810	26	52.3 mm	48.2 mm	30.4 mm
RND 205-00813	34	62.4 mm	58.4 mm	40.6 mm
RND 205-00816	40	70.1 mm	66 mm	48.2 mm

