

## Datenblatt / Data Sheet

### T5 Wedge Base Lamp (Dome)



Artikelnr.	Diameter Length	Color	Volts AC/DC	Base	Design Current (mA)	Wave Length (nm)	Lumens	Life time (h)	View Angle
70112200	T5*20mm	Red	6V	W2*4.6d	16±2mA	620-630	0.7 lm	30K (h)	60°
70112202	T5*20mm	Red	12V	W2*4.6d	16±2mA	620-630	0.7 lm	30K (h)	60°
70112208	T5*20mm	Red	24-28V	W2*4.6d	17±2mA	620-630	0.8 lm	30K (h)	60°
70112210	T5*20mm	Green	6V	W2*4.6d	16±2mA	515-525	1.8 lm	30K (h)	60°
70112212	T5*20mm	Green	12V	W2*4.6d	16±2mA	515-525	1.8 lm	30K (h)	60°
70112218	T5*20mm	Green	24-28V	W2*4.6d	17±2mA	515-525	1.9 lm	30K (h)	60°
70112230	T5*20mm	Yellow	6V	W2*4.6d	16±2mA	585-595	0.3 lm	30K (h)	60°
70112232	T5*20mm	Yellow	12V	W2*4.6d	16±2mA	585-595	0.3 lm	30K (h)	60°
70112238	T5*20mm	Yellow	24-28V	W2*4.6d	17±2mA	585-595	0.4 lm	30K (h)	60°
70112240	T5*20mm	White	6V	W2*4.6d	16±2mA	(K)5000-6000	1.9 lm	30K (h)	60°
70112242	T5*20mm	White	12V	W2*4.6d	16±2mA	(K)5000-6000	1.9 lm	30K (h)	60°
70112248	T5*20mm	White	24-28V	W2*4.6d	17±2mA	(K)5000-6000	2.0 lm	30K (h)	60°