




**Material & finish**  
 SHELL: Steel Zinc plated  
 PIN CONTACT: Brass Gold flash selective gold plated  
 INSULATOR: PBT & Glass-fibre reinforced UL 94V-0 Blue  
 NUMBER OF CONTACT: 14,24,36,50  
 CURRENT RATING: 5 Amp  
 DIELECTRIC STRENGTH: 1000V for one minute  
 INSULATOR RESISTANCE: 1000M Min. (at 500V DC)  
 TEMPERATURE: -55°C to +105°C



**Dimensions**

Positions	A	B	C	D
14	12.96	25.2	36.0	44.1
24	23.76	36.0	46.8	54.9
36	36.72	48.9	59.7	67.9
50	51.84	64.1	74.9	83.0

**CENTRONIC SOLDER FEMALE TYPE  
WITH SPRING LATCH**

RoHS compliant

Scale	1:1						Date	Name	Customer-No.
TOLERANCE							Drawn	30.06.2009	Dean
X.	±0.38						Approved	30.06.2009	Hellwig
X.X	±0.25								
X.XX	±0.13								
Angle	TOL								Drawing-No.
X°	±3°								ASS 0680 CO
.X°	±1.0°	①	Drawn	30.06.2009	Dean			rev01	
		Id.	Modification	Date	Name			Replace	Sheet

ASSMANN WSW-No. **A-57/xx F**