


PXF6051AAF Datasheet

Product Name // 100 M, OM3 Multi Mode, Cabled, Inline fiber connector

[View Product Page](#)



// Product Description:

- ⊞ Inline Fiber Connector to LC type connector
- ⊞ Sealed to IP66, IP68, IP69K when mated with compatible connector
- ⊞ no cable options, or pre-terminated from 5M - 450M available
- ⊞ Duplex LC type fiber connector
- ⊞ Choices of OS1, OM1 and OM3 cables for single or multimode
- ⊞ PXP6081 Sealing Cap available separately to maintain IP rating of unmated connectors
- ⊞ Mate with flex fiber connector PXF6050

// General Information:

| | |
|---------------------------------|--|
| Product Configurator: | No |
| Product Display Title: | Inline Fiber Connector to LC type Connector |
| Product Family: | Circular Fiber Connectors |
| Product Series: | 6000 Series - Duplex LC Fiber Buccaneer |
| Pdfbuilder Enabled: | Yes |
| Diameter Over Coupling Ring Mm: | 32mm |
| Fibre Mode: | OM3 |
| Function: | Inline to Double LC Connector Double Ended Fiber Cable |
| Ip Rating: | IP66, IP68, IP69K |
| Max Operating Temperature: | +70°C |
| Min Operating Temperature: | -25°C |
| Product Technical Image: | /p/x/pxf6051xxx_diagram.jpg |
| Package Id: | 564 |

// Electrical Specifications:

| | |
|---------------|----------|
| Contact Type: | LC Fiber |
|---------------|----------|

// Mechanical Specifications:

| | |
|----------------|--------------------|
| Coupling Type: | 30 Degree coupling |
|----------------|--------------------|

// Material Information:

| | |
|---------------------|----------------|
| Body Material: | Polyamide (PA) |
| Flamability Rating: | UL94V-0 |

// Product PDF Links

[6000 Series Fiber connectors...](#)

// Product 3D CAD Model Links

[PXF6051AAF3D CAD Model](#)