

## 12V Flexiprint


Ultra bright (5730)

### Specifications




Voltage	12V
Current	4.5A
Wattage	21.6W/m
Number of LED's	225pcs
Length of Stripe	2.5m
Operating Temperature	-25°~+60°C
Storage Temperature	-40°~+80°C
Viewing Angle	110°
CE/RoHS compliant	

### Benefits


Adhesive tape on backside  
cutable every ~33.3mm



### Electrical and Optical Characteristics (Ta=25°C)

Part Number	Colour	Wavelength / CCT	Intensity lm (typ.)	EEC
FP4-N01B-250	 warm-white	2800-3100°K	3600	A
FP4-S01B-250	 natural-white	3800-4250°K	4275	A
FP4-W01B-250	 white	5500-6500°K	4275	A

### Dimensions



Thickness: 2 mm +0.5

Sloan\_03\_GK\_LED-Modules\_15B

1. All dimensions are in millimetres
2. Tolerance is  $\pm 0.25$ mm unless otherwise specified
3. Specifications are subject to change without notice

Please also take note of our **General Information for Flexiprint and LED Modules**