



Ordering information & dimensions:

Specifications:

Current rating	5A AC, DC
Voltage rating	250V AC, DC
Temperature range	-25° to +85°C
Contact resistance	10mΩ max.
Insulation resistance	100MΩ min.
Withstanding voltage	1500V AC/minute
Pin material	Brass/Tin-plated
Material	PBT30%GF, UL94V-0
Colour	Natural (Black)

No. of pins	Dimensions	
	A	B
2 x 1	-	6.65
2 x 2	3.00	9.65
2 x 3	6.00	12.65
2 x 4	9.00	15.65
2 x 5	12.00	18.65
2 x 6	15.00	21.65
2 x 7	18.00	24.65
2 x 8	21.00	27.65
2 x 9	24.00	30.65
2 x 10	27.00	33.65
2 x 11	30.00	36.65
2 x 12	33.00	39.65

